AF™ GOLD R3

AF™-L Wire Tech, RECIPROCATING ONE-File System



FEATURES:

- * AF™-L Wire Tech
- * Reciprocating, CCWI50. CW30
- * greater resistance to cyclic fatigue
- * improves file flexibility, while still retaining cutting efficiency

	21mm	25mm	31mm	Taper	Siz∈
AFGR20	AFGR2021	AFGR2025	AFGR2031	06	#20
AFGR25	AFGR2521	AFGR2525	AFGR2531	06	#25
AFGR40	AFGR4021	AFGR4025	AFGR4031	06	#40

GUIDELINES FOR USE:

- * Explore the canal by using #10, stainless steel hand files
- * Irrigate, then expand a glide path by C-PATH FILE #16,.
- * In the presence of an irrigant, initiate shaping procedures starting with the AFGR25 file.
- * Use a gentle inward motion without pressure, with short I-2 mm amplitude strokes, remove the instrument from the canal after 3 pecks.
- * Clean the debris from the flute.
- * Use #IO K file to recapitulate the canal.
- * Repeat step 4, 5, 6, until approximately 2/3 of the working length has been reached.
- * Determine the working length again.
- * Use AFGR25 to the working length.
- * Use AFGR20 or AFGR40 for narrow or wide canals.
- * Single use recommended.